

80mm Receipt Paper Barcode Thermal Printer with USB+LAN+Serial port (Model No.: OCPP-80H)

Features:

Desktop or wall-mounted type for option.
 Supports multi 1D barcodes and 2D codes printing.
 USB+RS232+LAN,3 interface
 300mm /S high printing Speed
 100M Ethernet port ultra high speed data transmission.
 Supports 256KB NV Logo storage and 2M big buffer memory.
 Supports black mark detection and order reminding function,
 Compatible with OPOS driver.

Technical parameters

Printing method:	Direct thermal
Printing speed:	300mm/s
Roll width:	79.5±0.5mm
Print diameter:	Φ80mm
Paper thickness:	0.06-0.08mm
Column capacity:	576dots/line512 Dots/line
Line's pacing :	3.75mmAdjustable by commands
Print command:	Compatible with the ESC/POS command
Interface type:	Serial+USB+LAN
Cutters life:	1million cuts
Print head life:	100 km
Input buffer :	2048Kbytes
NV Flash:	256Kbytes
Power adaptor:	AC110V/240V50~60Hz
Power supply:	DC 24V/2.5A
Cash drawer supply:	DC 24V/1A
Work environment:	Temperature(0~45) humidity(10~80%)Non- condense
Work environment:	Temperature(0-45) degree centigrade, humidity(10-80%) Non- condense
Storage environment:	Temperature(-10~60°C); Humidity(10~90%)
Character size:	ANKFontA:1.5*3.0mm/ FontB1.1*2.1mm
Barcode:	UPC-A/UPC-E/JA/EAN13/JAN8/EAN8/CODE39/ITF/CODE93/CODE128/QRCode/PDF417 (options)
Characters:	PC347Standard EuropeKatakanaPC850MultilingualPC860PortuguesePC863Canadian-FrenchPC865NordicWest EuropeGreekHebrewEast EuropeIranWPC1252PC866Cyrillic#2PC852Latin2PC858IranIIatvianArabicPT1511251



OCPP-80H





OCPP-80H





OCPP-80H





OCPP-80H



Attention: Press FEED or re-start to reset cutter when it or cover stuck, if not, open here and turn the gear to reset cutter





FAQ

1. MOQ policy

No MOQ limitation for the standard products, but the unit price is different, bigger quantity better price.

For customized production, you can discuss the MOQ with our sales representative directly.

2. Sample Availability & Policy

After customers confirmed the specification, we are very glad to provide samples for testing and qualification.

All samples should be paid before shipment, the samples price is a higher than mass order. When the mass order placed, we can return you the samples cost, or send you more piece products with the shipments.

You can buy the samples from us directly using t/t, western union, or paypal. And you can also buy it on our

online store at aliexpress:http://www.aliexpress.com/store/403448?tracelog=minisite_CI.

3. Warranty

OCOM is dedicated to providing most cost-effective products and services with reliable quality that will meet customers' satisfaction;

We were qualified by global fortune 500 company, and we have the top 1 level trade assurance which 100% protect your money and lead time.

Our warranty of the products is about 12+1 months from the shipment normally, some designated models can have as long as 24 months warranty;

Any product within 30 days of delivery failure occurs shall be deemed invalid delivery (DOA). DOA products will give priority to the replacement, and shipped by courier.

For mass order, we would like to supply some spare parts with shipment for local quick repair. And after that, you can return failure parts for rework and analysis.

4. Payment Terms

For mass order, you can pay us by using T/T, LC, Western Union, Escrow or others. About samples order, T/T, Western Union, Escrow, Paypal are acceptable. Escrow Service is powered by Alipay.com. Currently, you can pay using Moneybookers, Visa, MasterCard and bank transfer. You can also pay with select debit cards including Maestro, Solo, Carte Bleue, PostePay, CartaSi, 4B and Euro6000.

5. Shipment

We accept all kinds of shipping ways including: express, air, sea, truck, or pick up by customers personally.

6. Customer

Our main customers from European, Australia, and the fast growing South America, Africa, Russia...

We have served more than 1300 customers from 133 countries, including the global fortune 500 company like Unilever, O2.....50 of them are the biggest distributor in the local territories.